



[Knowledgebase](#) > [Power Management](#) > [easYgen-3000XT](#) > [easYgen-3000XT PWM settings for CAT ADEM interfacing](#)

easYgen-3000XT PWM settings for CAT ADEM interfacing

Justin Schneider - 2026-07-27 - [easYgen-3000XT](#)

easYgen's PWM PID output signal need to set to min 50% and max 85% (parameter 5208 and 5209) when a CAT ADEM ECM is connected.

The screenshot displays the configuration interface for the EG3500XTP2 2.12-1_51263 device. The left sidebar shows a tree view of the configuration structure, with the 'Configure analog outputs' section expanded, highlighting 'Analog output 1'. The main panel on the right shows the configuration for '5200 AM Data source AO1'. The settings are as follows:

Parameter	Value
5201 Selected hardware type	PWM
5203 Filter time constant	Off
5204 Source value at minimum level	0
5206 Source value at maximum level	100
5208 Minimum hardware level	0
5209 Maximum hardware level	100
5210 PWM output level	10 V