



[Knowledgebase](#) > [Power Management](#) > [easYgen-3000XT](#) > [Why upgrading old easYgen-3200 to new easYgen-3200XT ?](#)

Why upgrading old easYgen-3200 to new easYgen-3200XT ?

Justin Schneider - 2026-07-27 - [easYgen-3000XT](#)

Many old easYgen-3200 variants (1 or 5A , P1 or P2 variants) can be replaced with only one P/N

Why switching to easYgen-3200XT?

SubD terminal Adapter

PLC

External Button

Start & Stop Buttons

Galvanic Isolator for AVR

easYgen-3200-P1/P2
4 different part numbers

CAN/E-Net Converter

Class 1 Transducer

Multiple interface Toolkit connectivity

Editable Screens

Poleslip Monitoring

Terminal Adapter Inbuilt for COM Ports

Illuminated Start & Stop Buttons inbuilt

Drop-In Replacement

Galvanic Isolation inbuilt up to 300V for AVR biasing

WAGO and PHOENIX CANopen based IO support

Enhanced Logic Manager

Language Editor Modbus Telegram Mapper

Redundant CAN/Ethernet connectivity

1x Modbus TCP Port/RS485

..1A & ..5A 100-480VAC sensing

Cost saving for entire control solution

Class 1 for kW

easYgen-3200XT
8440-2082

Additional external 32DI, 32DO, 16AI + 4AO via CANopen

WOODWARD
Always Innovating for a Better Future

PROPRIETARY INFORMATION - © 2016 WOODWARD, INC.

Please consider the documents here for more information:

[Download here](#)